

## PERFECT QUALITY FROM THE BEGINNING TO THE END

From empty to full, inside to outside, non-brand to correct brand, contaminated to uncontaminated, unlabelled to perfectly dressed, unattractive to attractive and premium to standard. Indeed from A to Z:

HEUFT establishes order, efficiency, quality and safety along returnable glass lines for filling beer from the beginning. Thorough sorting out for absolute brand purity is immediately followed by a continuous empty bottle inspection. It even makes that visible which cannot be seen at all using unique X-ray strobes: for example the smallest glass splinters. Thus ensuring a clean and safe journey to the filler. A careful foreign object inspection then awaits the full bottles. It does not miss any dangerous objects regardless of whether they are lying on the base or floating around in the drink. Finally a detailed label inspection ensures that the end product looks perfect.



# **SHOWROOM**

# **TRAINING**

# **SERVICE**

# **CONFERENCES**

systems — even with live tests using but also directly at the device! products from your own portfolio upon

> Visit@heuft.com +49 2636 56 0

Experience the complete range of The right know-how for reliable The nerve centre for a proactive From seminar room to auditorium for HEUFT solutions in action: our arena operation: experienced experts will customer service: our service control 199 quests: we are pleased to make with almost 1,000 square metres of provide you with all the knowledge centre coordinates all the services on our premises containing state-of-theexhibition space provides you with the you need in order to safeguard the your premises from online remote art multimedia equipment available perfect conditions to convince your—functionality and availability of your maintenance with the HEUFT to customers and partners for meetings self of the superior performance of HEUFT system sustainably in the HEUFT TeleService, the HEUFT PhoneService and events — including a tour of the our inspection and quality assurance Training Center – not only theoretically up to HEUFT DirectService visits – premises, specialist lectures and

> Training@heuft.com +49 2636 56 2671

for a worldwide 24/7 support.

Technical.Desk@heuft.com +49 2636 56 278

Welcome@heuft.com +49 2636 56 0

practical presentations!









## **HEUFT SYSTEMTECHNIK GMBH**

Am Wind 1 · 56659 Burgbrohl · Germany · heuft.com · info@heuft.com

GLASS BOTTLE INSPECTION

# HEUFT SX

Empty bottle sorting for full brand purity.

## More efficiency and productivity

Precise sorting out of non-brand bottles, reliable prevention of faulty filling, standstills and production downtimes.

## High degree of detection reliability

Reliable detection of non-brand bottle types and colours, safe identification of sealed and unsealable bottles as well as clear differentiation between glass and PET.

### Minimum false rejection rate

Accurate rejection due to the combined evaluation of all the measuring results using fuzzy logic.



# HEUFT eXaminer II XOS

Foreign object inspection of the new generation with optical technologies and unique X-ray strobes.

#### Broad spectrum

From glass splinters, mould to transparent film: the reliable detection of high density and low density foreign objects in full containers.

## Complete inspection without blind spots

Continuous inspection of the total container volume.

## X-ray flash instead of a permanent beam

## Sharp images with minimum radiation.

## Less false rejections

Highly precise product tracking and the HEUFT *reflexx*<sup>2</sup> real-time image processing system with learning ability for clearly differentiating between real and supposed safety risks.

# HEUFT InLine II IXS

X-ray assisted premium empty bottle inspection of the new generation.

## Unprecedented detection reliability

The highest ever detection performance at the lowest false rejection rate confirmed by independent experts. Reliable detection, even of glass splinters in residual liquid, with minimum radiation due to unique X-ray strobes. Innovative full-field image converters for even more sensitivity.

### Continuous optical examination

Innovative infeed check with shape detection for more efficiency. Exact fine bottle alignment for considerably more than 360° coverage during the sidewall inspection with doubled resolution. Even more precise base, thread, underchip and finish inspection. Integrated residual liquid detections.

## Solid construction

Modular design in accordance with the HEUFT *CleanDesign*. Optimal arrangement and safe housing of all the detection units.

### Simply resource saving

HEUFT SPECTRUM <sup>II</sup> system with self-explanatory HEUFT NaVi user guidance and fully automatic brand changes. HEUFT reflexx<sup>2</sup> real-time high-performance image processing system with teach-in function.



# HEUFT FinalView LBL

Label inspection for perfectly dressed end products.

## Perfect visual appearance

Continuous complete inspection of all the labels with the reliable identification and rejection of mislabelled bottles.

## Maximum detection reliability

Reliable detection of crooked, non-brand, creased and torn labels as well as the clear identification of design faults due to superior optical technologies and the HEUFT reflexx<sup>2</sup> image processing system with teach-in assistant.

## Optimal adaptation

Adaptive LED illumination for detection pictures without shadows or reflections and optional add-on cameras for different container types and sizes.

## Uncomplicated brand changes

Automatic adjustment of the transport and detection units.